



6 STAGES R&D ISOLATOR

- 6 working areas
- Negative pressure in respect with laboratory environment
- High containment suitable for OEB5 products
- Customized project for an increased ergonomic design
- Fully PLC controlled to minimize human errors
- Fully washable with organic solvents to eliminate any trace of product
- Integrated vacuum dryer
- Several integrated utilities such as dry-scroll vacuum pump and pressurized washing liquids (organic solvents)
- Turbulent flow with nitrogen and O₂ monitoring.



6 STAGES R&D ISOLATOR



1. Integrated continuous liner
2. Spray gun and RTP port
3. Utility: dry scroll vacuum pumps
4. Integrated vacuum dryer
5. Internal sliding doors with EPDM FDA certified gasket
6. Utility: integrated washing circuit